




# Technical Data

# LinerMate® ACCESSORY

# 3944-134



### MATERIALS:

**LinerMate Accessory** — Molded plastic sleeve and U-shaped, 18-8, type-304, 20-gauge (.91mm) stainless steel support strap hemmed for safety; riveted construction. Rests inside of waste receptacle area, removable for servicing. Fits Bobrick and most other manufacturers' comparable 12-gal. capacity receptacles.

| Applications   | Model Numbers  | Part No.  |
|--|--|-----------|
| <b>Bobrick ClassicSeries®</b>  | B-3644, B-3942, B-3944, B-3949, B-3961, B-39619, B-3974, B-3979  | 3944-134  |
| <b>Gamco TW and WR Series</b>  | TW-1, TW-1-6, TW-1F, TW-1FS, TW-14RP, WR-6, WR-14  | 3944-134  |
| <b>Other Manufacturers</b>   | LinerMate fits most other manufacturers' similar 12-gal waste receptacles with the following minimum dimensions:<br>22-3/8" H x 14-13/16" W x 6-7/8" D (570 x 375 x 175mm) | 3944-134  |
| <b>Bobrick ConturaSeries®</b><br>(For retrofit into units manufactured prior to Jan. 2010) | B-277  | 3944-134  |
|  | B-43644  | 43644-134 |
|  | B-4369, B-43699  | 4369-134  |
|  | B-43944, B-43949   | 43944-134 |

### OPERATION:

To insert disposable can liner, lift LinerMate up and forward from waste receptacle and rest over front edge with the bottom notches of LinerMate sleeve engaged on top front edge of receptacle. Place disposable liner inside LinerMate and fold trash liner over LinerMate sleeve. Tie a knot in the corner of the can liner, then place LinerMate with disposable liner back into receptacle. To empty, gather disposable liner from LinerMate sleeve and lift bag up.

### INSTALLATION:

If hooks exist in waste receptacle, carefully bend them in or push in to clear obstruction for LinerMate. Insert LinerMate inside 12-gal. waste receptacle.

### SPECIFICATION:

LinerMate accessory for ClassicSeries 12-gal. waste receptacle shall have a molded plastic sleeve with a 20-gauge (.91mm) stainless steel, U-shaped support strap, hemmed for safety; riveted construction. LinerMate facilitates installation and removal of disposable liners without unsightly liner overhang. LinerMate shall rest inside of waste receptacle. LinerMate fits most other manufacturers' similar 12-gal. waste receptacles with the following minimum dimensions: 22-3/8" H x 14-13/16" W x 6-7/8" D (570 x 375 x 175mm).

**LinerMate Trash Liner Holder shall be Model 3944-134 of Bobrick Washroom Equipment, Inc., Clifton Park, New York; Jackson, Tennessee; Los Angeles, California; Bobrick Washroom Equipment Company, Scarborough, Ontario; Bobrick Washroom Equipment Pty. Ltd., Australia; and Bobrick Washroom Equipment Limited, United Kingdom.**